AH-PAS Abstandshülsen aus Kunststoff

ArtNr.	D (mm)	d (mm)				L (n	nm)			
101 27 XX	6,0	4,1	2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
			10,0	11,0	12,0	13,0	14,0	15,0	16,0	17,0
			18,0	19,0 27,0	20,0	21,0 29,0	22,0	23,0	24,0 32,0	25,0 33,0
			26,0 34,0	35,0	36,0	37,0	30,0	39,0	40,0	41,0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0	54,0			,
101 46 XX	7,0	3,4	2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
			10,0	11,0	12,0	13,0	14,0	15,0	16,0	17,0
			18,0	19,0	20,0	21,0	22,0	23,0	24,0	25,0
			26,0 34,0	27,0 35,0	28,0 36,0	29,0 37,0	30,0 38,0	31,0 39,0	32,0 40,0	33,0 41,0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0	54,0	55,0	56,0	57,0
			58,0	59,0	60,0					
101 13 XX	7,0	4,5	2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
			10,0	11,0	12,0	13,0	14,0	15,0	16,0	17,0
			18,0	19,0 27,0	20,0	21,0 29,0	22,0 30,0	23,0 31,0	24,0 32,0	25,0 33,0
			34,0	35,0	36,0	37,0	38,0	39,0	40.0	41.0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0	54,0	55,0	56,0	57,0
			58,0	59,0	60,0					
101 53 XX	7,0	5,0	2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
			10,0	11,0	12,0	13,0	14,0	15,0	16,0	17,0
			18,0 26,0	19,0 27,0	20,0 28,0	21,0 29,0	22,0 30,0	23,0	24,0 32,0	25,0 33,0
			34,0	35,0	36,0	37,0	38,0	39,0	40,0	41,0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0				
101 22 XX	8,0	4,2	2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
			10,0	11,0	12,0	13,0	14,0	15,0	16,0	17,0
			18,0	19,0	20,0 28,0	21,0	22,0 30,0	23,0	24,0	25,0 33,0
			26,0 34,0	27,0 35,0	36,0	29,0 37,0	38,0	39,0	32,0 40,0	41,0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0	54,0	55,0	56,0	57,0
			58,0	59,0	60,0					
101 69 XX			2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
			10,0	11,0	12,0	13,0	14,0	15,0	16,0	17,0
			18,0 26,0	19,0 27,0	20,0	21,0 29,0	22,0 30,0	23,0	24,0 32,0	25,0 33,0
	8,0	5,2	34,0	35,0	36,0	37,0	38,0	39,0	40,0	41,0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0	54,0	55,0	56,0	57,0
			58,0	59,0	60,0	<u> </u>				
404 OF VV	10.0	2.0	2,0	3,0	4,0	5,0	6,0	7,0	8,0	9,0
101 65 XX	10,0	3,2	10,0	11,0 19,0	12,0 20,0	13,0	14,0	15,0	16,0	17,0
						1 50	0.0	7.0		0.0
101 14 XX	10,0	5,2	2,0	3,0	4,0 12,0	5,0 13,0	6,0	7,0 15,0	8,0 16,0	9,0 17,0
			18,0	19,0	20,0	21,0	22,0	23,0	24,0	25,0
			26,0	27,0	28,0	29,0	30,0	31,0	32,0	33,0
			34,0	35,0	36,0	37,0	38,0	39,0	40,0	41,0
			42,0 50,0	43,0 51,0	44,0 52,0	45,0 53,0	46,0 54,0	47,0 55,0	48,0 56,0	49,0 57,0
101 09 XX	10,0	6,2	2,0	3,0	4,0 12,0	5,0 13,0	6,0 14,0	7,0 15,0	8,0 16,0	9,0 17,0
			18,0	19,0	20,0	21,0	22,0	23,0	24,0	25,0
			26,0	27,0	28,0	29,0	30,0	31,0	32,0	33,0
			34,0	35,0	36,0	37,0	38,0	39,0	40,0	41,0
			42,0	43,0	44,0	45,0	46,0	47,0	48,0	49,0
			50,0	51,0	52,0	53,0	54,0	55,0		

Bitte bei der Bestellung XX durch Länge "L" ersetzen, z.B. Länge 2 mm = 101 28 02.

